

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257940

Luminaire Tested: P3AS17R659040DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659040DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1713.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257940
CATALOG NUMBER: P3AS17R659040DE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1257940
 CATALOG NUMBER: P3AS17R659040DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	418629
5°	393990
10°	388993
15°	382113
20°	360788
25°	334858
30°	260293
35°	150577
40°	60685
45°	27910
50°	10882
55°	4244
60°	3640
65°	3580
70°	3526
75°	3558
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27910 cd/sqm



TEST NUMBER: P1257940
 CATALOG NUMBER: P3AS17R659040DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.2	9.9
10°-20°	470.0	27.4
20°-30°	615.3	35.9
30°-40°	356.4	20.8
40°-50°	76.3	4.5
50°-60°	12.4	0.7
60°-70°	6.8	0.4
70°-80°	4.0	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.5	73.3
0°-40°	1611.9	94.1
0°-60°	1700.6	99.3
0°-90°	1713.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1713.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1909	
5°	1790	170
15°	1683	470
25°	1384	615
35°	562	356
45°	90	76
55°	11	12
65°	7	7
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P1257940
CATALOG NUMBER: P3AS17R659040DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1909.1
2.5°	1855.0
5°	1789.9
7.5°	1763.6
10°	1747.0
12.5°	1723.4
15°	1683.2
17.5°	1620.9
20°	1546.1
22.5°	1475.4
25°	1384.0
27.5°	1230.2
30°	1028.0
32.5°	796.6
35°	562.5
37.5°	356.0
40°	212.0
42.5°	133.0
45°	90.0
47.5°	58.2
50°	31.9
52.5°	15.2
55°	11.1
57.5°	9.7
60°	8.3
62.5°	8.3
65°	6.9
67.5°	5.5
70°	5.5
72.5°	4.2
75°	4.2
77.5°	2.8
80°	2.8
82.5°	1.4
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)