

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258588

Luminaire Tested: P3AS24R559040D010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R559040D010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2264.0 lumens  
Efficiency: N/A  
Efficacy: 78.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258588  
CATALOG NUMBER: P3AS24R559040D010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1258588

CATALOG NUMBER: P3AS24R559040D010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	621683
5°	615363
10°	594266
15°	549311
20°	474011
25°	374368
30°	265585
35°	171243
40°	102850
45°	57960
50°	31180
55°	11125
60°	9999
65°	9703
70°	9296
75°	8811
80°	7829
85°	5284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 57960 cd/sqm



TEST NUMBER: P1258588  
 CATALOG NUMBER: P3AS24R559040D010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	262.9	11.6
10°-20°	669.1	29.6
20°-30°	701.2	31.0
30°-40°	409.1	18.1
40°-50°	153.1	6.8
50°-60°	36.0	1.6
60°-70°	18.5	0.8
70°-80°	11.0	0.5
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1633.2	72.1
0°-40°	2042.3	90.2
0°-60°	2231.4	98.6
0°-90°	2264.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2264.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2835	
5°	2796	263
15°	2420	669
25°	1547	701
35°	640	409
45°	187	153
55°	29	36
65°	19	18
75°	10	11
85°	2	3
90°	0	



TEST NUMBER: P1258588  
CATALOG NUMBER: P3AS24R559040D010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2835.1
2.5°	2826.8
5°	2795.6
7.5°	2745.8
10°	2668.9
12.5°	2560.9
15°	2419.7
17.5°	2241.1
20°	2031.3
22.5°	1796.6
25°	1547.3
27.5°	1291.9
30°	1048.9
32.5°	828.7
35°	639.7
37.5°	486.0
40°	359.3
42.5°	257.5
45°	186.9
47.5°	135.0
50°	91.4
52.5°	51.9
55°	29.1
57.5°	24.9
60°	22.8
62.5°	20.8
65°	18.7
67.5°	16.6
70°	14.5
72.5°	12.5
75°	10.4
77.5°	8.3
80°	6.2
82.5°	4.2
85°	2.1
87.5°	2.1
90°	0.0

(END OF REPORT)