

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257963

Luminaire Tested: P3AS17R659040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 471.0 lumens
Efficiency: N/A
Efficacy: 22.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257963
CATALOG NUMBER: P3AS17R659040DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1257963
 CATALOG NUMBER: P3AS17R659040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119727
5°	116729
10°	108704
15°	97435
20°	84147
25°	69996
30°	55198
35°	40903
40°	28196
45°	17490
50°	9484
55°	5964
60°	5043
65°	4566
70°	3911
75°	3474
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17490 cd/sqm



TEST NUMBER: P1257963
 CATALOG NUMBER: P3AS17R659040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	10.5
10°-20°	119.3	25.3
20°-30°	131.9	28.0
30°-40°	95.8	20.3
40°-50°	44.9	9.5
50°-60°	15.1	3.2
60°-70°	8.7	1.9
70°-80°	4.6	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.4	63.8
0°-40°	396.2	84.1
0°-60°	456.2	96.9
0°-90°	471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	471.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	546	
5°	530	49
15°	429	119
25°	289	132
35°	153	96
45°	56	45
55°	16	15
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1257963
CATALOG NUMBER: P3AS17R659040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	546.0
2.5°	542.6
5°	530.3
7.5°	512.0
10°	488.2
12.5°	460.4
15°	429.2
17.5°	395.2
20°	360.6
22.5°	324.6
25°	289.3
27.5°	253.3
30°	218.0
32.5°	184.0
35°	152.8
37.5°	124.3
40°	98.5
42.5°	75.4
45°	56.4
47.5°	40.7
50°	27.8
52.5°	19.0
55°	15.6
57.5°	13.6
60°	11.5
62.5°	10.2
65°	8.8
67.5°	7.5
70°	6.1
72.5°	5.4
75°	4.1
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)