

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258590

Luminaire Tested: P3AS24R559040D010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R559040D010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1758.0 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258590
CATALOG NUMBER: P3AS24R559040D010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1258590
 CATALOG NUMBER: P3AS24R559040D010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	330544
5°	326325
10°	313466
15°	293191
20°	267447
25°	238635
30°	208716
35°	173411
40°	136713
45°	92723
50°	56663
55°	29361
60°	27322
65°	25839
70°	23978
75°	21096
80°	20962
85°	15599

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 92723 cd/sqm



TEST NUMBER: P1258590
 CATALOG NUMBER: P3AS24R559040D010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.0	7.9
10°-20°	361.0	20.5
20°-30°	452.0	25.7
30°-40°	403.5	23.0
40°-50°	236.3	13.4
50°-60°	81.6	4.6
60°-70°	49.3	2.8
70°-80°	27.4	1.6
80°-90°	7.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.0	54.2
0°-40°	1355.5	77.1
0°-60°	1673.4	95.2
0°-90°	1758.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1758.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1507	
5°	1482	139
15°	1292	361
25°	986	452
35°	648	403
45°	299	236
55°	77	82
65°	50	49
75°	25	27
85°	6	8
90°	0	



TEST NUMBER: P1258590
CATALOG NUMBER: P3AS24R559040D010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1507.4
2.5°	1499.1
5°	1482.5
7.5°	1449.3
10°	1407.8
12.5°	1355.9
15°	1291.5
17.5°	1223.0
20°	1146.1
22.5°	1067.2
25°	986.3
27.5°	905.3
30°	824.3
32.5°	737.1
35°	647.8
37.5°	560.6
40°	477.6
42.5°	388.3
45°	299.0
47.5°	228.4
50°	166.1
52.5°	108.0
55°	76.8
57.5°	68.5
60°	62.3
62.5°	56.1
65°	49.8
67.5°	43.6
70°	37.4
72.5°	31.1
75°	24.9
77.5°	20.8
80°	16.6
82.5°	10.4
85°	6.2
87.5°	4.2
90°	0.0

(END OF REPORT)