

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258828

Luminaire Tested: P3AS02R259050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 171.0 lumens
Efficiency: N/A
Efficacy: 47.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258828

CATALOG NUMBER: P3AS02R259050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1258828

CATALOG NUMBER: P3AS02R259050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62078
5°	59564
10°	52170
15°	41930
20°	32226
25°	24389
30°	17623
35°	11698
40°	7099
45°	4124
50°	2627
55°	2141
60°	1886
65°	1660
70°	1346
75°	1356
80°	1010
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4124 cd/sqm

TEST NUMBER: P1258828

CATALOG NUMBER: P3AS02R259050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.6	14.4
10°-20°	51.1	29.9
20°-30°	46.2	27.0
30°-40°	27.7	16.2
40°-50°	11.0	6.4
50°-60°	5.1	3.0
60°-70°	3.1	1.8
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	121.9	71.3
0°-40°	149.7	87.5
0°-60°	165.8	96.9
0°-90°	171.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	171.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	283	
5°	271	25
15°	185	51
25°	101	46
35°	44	28
45°	13	11
55°	6	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1258828

CATALOG NUMBER: P3AS02R259050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	283.1
1°	283.1
2°	281.8
3°	278.9
4°	275.1
5°	270.6
6°	264.7
7°	258.1
8°	250.3
9°	242.6
10°	234.3
11°	224.7
12°	214.9
13°	205.0
14°	195.1
15°	184.7
17.5°	160.2
20°	138.1
22.5°	118.1
25°	100.8
27.5°	84.5
30°	69.6
32.5°	56.0
35°	43.7
37.5°	33.3
40°	24.8
42.5°	18.1
45°	13.3
47.5°	10.1
50°	7.7
52.5°	6.4
55°	5.6
57.5°	4.8
60°	4.3
62.5°	3.5
65°	3.2
67.5°	2.7
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.3
80°	0.8
82.5°	0.5
85°	0.5
87.5°	0.3



TEST NUMBER: P1258828

CATALOG NUMBER: P3AS02R259050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)