

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258855

Luminaire Tested: P3AS02R309050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 84.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258855

CATALOG NUMBER: P3AS02R309050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1258855

CATALOG NUMBER: P3AS02R309050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28704
5°	27801
10°	25050
15°	20727
20°	16055
25°	12049
30°	8736
35°	5836
40°	3578
45°	2109
50°	1296
55°	1032
60°	921
65°	726
70°	641
75°	678
80°	505
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2109 cd/sqm

TEST NUMBER: P1258855

CATALOG NUMBER: P3AS02R309050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.6	13.8
10°-20°	25.1	29.9
20°-30°	22.9	27.2
30°-40°	13.8	16.5
40°-50°	5.6	6.6
50°-60°	2.4	2.9
60°-70°	1.5	1.7
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	59.7	71.0
0°-40°	73.5	87.5
0°-60°	81.5	97.0
0°-90°	84.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	84.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	131	
5°	126	12
15°	91	25
25°	50	23
35°	22	14
45°	7	6
55°	3	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1258855

CATALOG NUMBER: P3AS02R309050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	130.9
1°	130.8
2°	130.3
3°	129.3
4°	128.0
5°	126.3
6°	124.3
7°	122.0
8°	119.2
9°	115.9
10°	112.5
11°	108.6
12°	104.5
13°	100.3
14°	95.7
15°	91.3
17.5°	79.7
20°	68.8
22.5°	58.6
25°	49.8
27.5°	41.7
30°	34.5
32.5°	27.9
35°	21.8
37.5°	16.7
40°	12.5
42.5°	9.1
45°	6.8
47.5°	5.1
50°	3.8
52.5°	3.0
55°	2.7
57.5°	2.3
60°	2.1
62.5°	1.7
65°	1.4
67.5°	1.3
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.7
80°	0.4
82.5°	0.3
85°	0.3
87.5°	0.1



TEST NUMBER: P1258855

CATALOG NUMBER: P3AS02R309050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)