

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258177

Luminaire Tested: P3AS20R459040D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258177  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R459040D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2438.0 lumens  
Efficiency: N/A  
Efficacy: 84.7 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258177  
CATALOG NUMBER: P3AS20R459040D010 E3CD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1258177

CATALOG NUMBER: P3AS20R459040D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	92	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	92	90	88	87
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	88	86	84	82
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	85	82	80	79
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	82	79	76	75
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	79	76	73	72
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	76	73	70	69
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	73	70	67	66
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	71	67	65	64
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1056999
5°	1062643
10°	1029997
15°	863138
20°	659807
25°	401660
30°	167114
35°	53538
40°	16660
45°	3380
50°	2490
55°	2791
60°	2412
65°	2854
70°	2308
75°	3050
80°	2273
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3380 cd/sqm



TEST NUMBER: P1258177  
 CATALOG NUMBER: P3AS20R459040D010 E3CD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	455.3	18.7
10°-20°	1045.0	42.9
20°-30°	752.4	30.9
30°-40°	156.5	6.4
40°-50°	14.3	0.6
50°-60°	5.9	0.2
60°-70°	4.7	0.2
70°-80°	3.1	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2252.7	92.4
0°-40°	2409.2	98.8
0°-60°	2429.5	99.6
0°-90°	2438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2438.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4820	
5°	4828	455
15°	3802	1045
25°	1660	752
35°	200	157
45°	11	14
55°	7	6
65°	6	5
75°	4	3
85°	0	1
90°	0	



TEST NUMBER: P1258177  
CATALOG NUMBER: P3AS20R459040D010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4820.3
2.5°	4822.2
5°	4827.6
7.5°	4793.1
10°	4625.8
12.5°	4276.7
15°	3802.1
17.5°	3316.6
20°	2827.5
22.5°	2265.6
25°	1660.1
27.5°	1094.6
30°	660.0
32.5°	369.1
35°	200.0
37.5°	112.7
40°	58.2
42.5°	25.5
45°	10.9
47.5°	7.3
50°	7.3
52.5°	7.3
55°	7.3
57.5°	5.5
60°	5.5
62.5°	5.5
65°	5.5
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)