

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258915

Luminaire Tested: P3AS02R409050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 96.0 lumens
Efficiency: N/A
Efficacy: 26.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258915

CATALOG NUMBER: P3AS02R409050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1258915

CATALOG NUMBER: P3AS02R409050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29888
5°	29298
10°	27276
15°	23769
20°	19158
25°	14348
30°	10103
35°	6612
40°	4008
45°	2388
50°	1433
55°	1147
60°	1053
65°	882
70°	833
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2388 cd/sqm

TEST NUMBER: P1258915

CATALOG NUMBER: P3AS02R409050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.4	12.9
10°-20°	28.8	30.0
20°-30°	27.2	28.3
30°-40°	15.7	16.4
40°-50°	6.3	6.5
50°-60°	2.8	2.9
60°-70°	1.7	1.8
70°-80°	0.9	0.9
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	68.4	71.2
0°-40°	84.1	87.6
0°-60°	93.1	97.0
0°-90°	96.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	96.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	136	
5°	133	12
15°	105	29
25°	59	27
35°	25	16
45°	8	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1258915

CATALOG NUMBER: P3AS02R409050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	136.3
2.5°	135.5
5°	133.1
7.5°	128.5
10°	122.5
12.5°	114.4
15°	104.7
17.5°	93.8
20°	82.1
22.5°	70.3
25°	59.3
27.5°	49.1
30°	39.9
32.5°	31.8
35°	24.7
37.5°	18.7
40°	14.0
42.5°	10.5
45°	7.7
47.5°	5.6
50°	4.2
52.5°	3.4
55°	3.0
57.5°	2.7
60°	2.4
62.5°	2.0
65°	1.7
67.5°	1.4
70°	1.3
72.5°	1.0
75°	0.8
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)