

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258936

Luminaire Tested: P3AS02R459050DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459050DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258936

CATALOG NUMBER: P3AS02R459050DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1258936

CATALOG NUMBER: P3AS02R459050DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48987
5°	48118
10°	45535
15°	41521
20°	36707
25°	31889
30°	27371
35°	22807
40°	17003
45°	10389
50°	4810
55°	3747
60°	3640
65°	3321
70°	3077
75°	2965
80°	2652
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10389 cd/sqm

TEST NUMBER: P1258936

CATALOG NUMBER: P3AS02R459050DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	8.8
10°-20°	50.9	22.0
20°-30°	60.5	26.2
30°-40°	52.6	22.8
40°-50°	26.4	11.4
50°-60°	9.2	4.0
60°-70°	6.4	2.8
70°-80°	3.6	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	131.8	57.1
0°-40°	184.4	79.8
0°-60°	219.9	95.2
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	223	
5°	219	20
15°	183	51
25°	132	61
35°	85	53
45°	34	26
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1258936

CATALOG NUMBER: P3AS02R459050DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	223.4
2.5°	222.3
5°	218.6
7.5°	212.7
10°	204.5
12.5°	194.3
15°	182.9
17.5°	170.1
20°	157.3
22.5°	144.3
25°	131.8
27.5°	119.8
30°	108.1
32.5°	96.9
35°	85.2
37.5°	72.7
40°	59.4
42.5°	46.3
45°	33.5
47.5°	22.1
50°	14.1
52.5°	10.9
55°	9.8
57.5°	9.1
60°	8.3
62.5°	7.5
65°	6.4
67.5°	5.6
70°	4.8
72.5°	4.0
75°	3.5
77.5°	2.7
80°	2.1
82.5°	1.6
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)