

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258957

Luminaire Tested: P3AS02R509050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 147.0 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258957

CATALOG NUMBER: P3AS02R509050DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1258957

CATALOG NUMBER: P3AS02R509050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	84		88	85	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	80	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	75	71		88	80	74	70		78	73	70		77	73	69		75	72	69
7	85	76	70	66		84	75	70	66		74	69	66		73	69	65		72	68	65
8	81	72	66	62		80	71	66	62		70	65	62		69	65	62		68	64	61
9	78	68	63	59		76	68	62	59		67	62	59		66	62	58		65	61	58
10	74	65	59	56		73	65	59	56		64	59	55		63	58	55		62	58	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46794
5°	45851
10°	42952
15°	38457
20°	32366
25°	24703
30°	16053
35°	9530
40°	5496
45°	2760
50°	1023
55°	803
60°	746
65°	675
70°	641
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2760 cd/sqm

TEST NUMBER: P1258957

CATALOG NUMBER: P3AS02R509050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.4	13.2
10°-20°	46.8	31.9
20°-30°	46.0	31.3
30°-40°	23.2	15.8
40°-50°	7.3	5.0
50°-60°	1.9	1.3
60°-70°	1.3	0.9
70°-80°	0.8	0.6
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.2	76.3
0°-40°	135.3	92.1
0°-60°	144.5	98.3
0°-90°	147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	213	
5°	208	19
15°	169	47
25°	102	46
35°	36	23
45°	9	7
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1258957

CATALOG NUMBER: P3AS02R509050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	213.4
2.5°	212.1
5°	208.3
7.5°	201.5
10°	192.9
12.5°	181.8
15°	169.4
17.5°	155.0
20°	138.7
22.5°	121.0
25°	102.1
27.5°	81.9
30°	63.4
32.5°	47.7
35°	35.6
37.5°	26.3
40°	19.2
42.5°	13.6
45°	8.9
47.5°	5.1
50°	3.0
52.5°	2.2
55°	2.1
57.5°	1.8
60°	1.7
62.5°	1.6
65°	1.3
67.5°	1.2
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)