

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258974

Luminaire Tested: P3AS02R509050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 196.1 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258974

CATALOG NUMBER: P3AS02R509050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1258974

CATALOG NUMBER: P3AS02R509050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57013
5°	55470
10°	51146
15°	44995
20°	37640
25°	29857
30°	21902
35°	15044
40°	9561
45°	5334
50°	2900
55°	2447
60°	2105
65°	1920
70°	1731
75°	1610
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5334 cd/sqm

TEST NUMBER: P1258974

CATALOG NUMBER: P3AS02R509050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.3	11.9
10°-20°	54.9	28.0
20°-30°	56.2	28.6
30°-40°	35.6	18.2
40°-50°	14.2	7.2
50°-60°	5.8	2.9
60°-70°	3.7	1.9
70°-80°	1.9	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	134.4	68.5
0°-40°	170.0	86.7
0°-60°	189.9	96.9
0°-90°	196.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	196.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	252	23
15°	198	55
25°	123	56
35°	56	36
45°	17	14
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1258974

CATALOG NUMBER: P3AS02R509050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	260.0
2.5°	258.1
5°	252.0
7.5°	242.5
10°	229.7
12.5°	214.6
15°	198.2
17.5°	180.1
20°	161.3
22.5°	142.5
25°	123.4
27.5°	104.3
30°	86.5
32.5°	70.6
35°	56.2
37.5°	44.0
40°	33.4
42.5°	24.7
45°	17.2
47.5°	11.7
50°	8.5
52.5°	7.2
55°	6.4
57.5°	5.6
60°	4.8
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.7
72.5°	2.1
75°	1.9
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)