

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258333

Luminaire Tested: P3AS20R709040D010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1258333  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R709040D010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1307.0 lumens  
Efficiency: N/A  
Efficacy: 45.4 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258333

CATALOG NUMBER: P3AS20R709040D010 E3DLP1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1258333

CATALOG NUMBER: P3AS20R709040D010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  |  | 93  | 90  | 88  |  | 90  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 83  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 84  |
| 4   | 95  | 86  | 80  | 76  | 93  | 85  | 80  | 75  | 83  | 78  | 74  |  | 81  | 77  | 73  |  | 79  |
| 5   | 89  | 80  | 74  | 69  | 88  | 79  | 73  | 69  | 78  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 6   | 85  | 75  | 68  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 62  | 58  |  | 67  | 62  | 58  |  | 66  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  |
| 10  | 69  | 58  | 52  | 48  | 67  | 58  | 52  | 48  | 57  | 51  | 48  |  | 56  | 51  | 48  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 306576 |
| 5°  | 300946 |
| 10° | 283762 |
| 15° | 257550 |
| 20° | 225280 |
| 25° | 190027 |
| 30° | 155594 |
| 35° | 120702 |
| 40° | 86390  |
| 45° | 54703  |
| 50° | 27291  |
| 55° | 16668  |
| 60° | 14341  |
| 65° | 13231  |
| 70° | 11669  |
| 75° | 10760  |
| 80° | 9218   |
| 85° | 9057   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 54703 cd/sqm

TEST NUMBER: P1258333

CATALOG NUMBER: P3AS20R709040D010 E3DLP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 127.6  | 9.8       |
| 10°-20°   | 315.7  | 24.2      |
| 20°-30°   | 359.5  | 27.5      |
| 30°-40°   | 281.1  | 21.5      |
| 40°-50°   | 138.1  | 10.6      |
| 50°-60°   | 42.5   | 3.2       |
| 60°-70°   | 25.2   | 1.9       |
| 70°-80°   | 13.4   | 1.0       |
| 80°-90°   | 4.0    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 802.7  | 61.4      |
| 0°-40°    | 1083.9 | 82.9      |
| 0°-60°    | 1264.4 | 96.7      |
| 0°-90°    | 1307.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1307.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1398 |      |
| 5°  | 1367 | 128  |
| 15° | 1134 | 316  |
| 25° | 785  | 360  |
| 35° | 451  | 281  |
| 45° | 176  | 138  |
| 55° | 44   | 42   |
| 65° | 26   | 25   |
| 75° | 13   | 13   |
| 85° | 4    | 4    |
| 90° | 0    |      |

TEST NUMBER: P1258333

CATALOG NUMBER: P3AS20R709040D010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1398.1 |
| 2.5°  | 1390.8 |
| 5°    | 1367.2 |
| 7.5°  | 1329.0 |
| 10°   | 1274.4 |
| 12.5° | 1210.8 |
| 15°   | 1134.5 |
| 17.5° | 1052.6 |
| 20°   | 965.4  |
| 22.5° | 874.5  |
| 25°   | 785.4  |
| 27.5° | 698.1  |
| 30°   | 614.5  |
| 32.5° | 530.9  |
| 35°   | 450.9  |
| 37.5° | 374.5  |
| 40°   | 301.8  |
| 42.5° | 234.5  |
| 45°   | 176.4  |
| 47.5° | 123.6  |
| 50°   | 80.0   |
| 52.5° | 52.7   |
| 55°   | 43.6   |
| 57.5° | 38.2   |
| 60°   | 32.7   |
| 62.5° | 29.1   |
| 65°   | 25.5   |
| 67.5° | 21.8   |
| 70°   | 18.2   |
| 72.5° | 14.5   |
| 75°   | 12.7   |
| 77.5° | 10.9   |
| 80°   | 7.3    |
| 82.5° | 5.5    |
| 85°   | 3.6    |
| 87.5° | 1.8    |
| 90°   | 0.0    |

(END OF REPORT)