

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259007

Luminaire Tested: P3AS02R609050DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609050DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 344.0 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259007
CATALOG NUMBER: P3AS02R609050DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1259007
 CATALOG NUMBER: P3AS02R609050DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82143
5°	78890
10°	81228
15°	82271
20°	72643
25°	61213
30°	49653
35°	32337
40°	14856
45°	5706
50°	1910
55°	497
60°	482
65°	415
70°	321
75°	424
80°	379
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5706 cd/sqm



TEST NUMBER: P1259007
 CATALOG NUMBER: P3AS02R609050DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.5	10.0
10°-20°	99.2	28.8
20°-30°	115.7	33.6
30°-40°	74.7	21.7
40°-50°	16.7	4.9
50°-60°	1.7	0.5
60°-70°	0.8	0.2
70°-80°	0.4	0.1
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.5	72.5
0°-40°	324.2	94.2
0°-60°	342.6	99.6
0°-90°	344.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	344.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	375	
5°	358	34
15°	362	99
25°	253	116
35°	121	75
45°	18	17
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1259007
CATALOG NUMBER: P3AS02R609050DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	374.6
2.5°	368.5
5°	358.4
7.5°	357.9
10°	364.8
12.5°	369.3
15°	362.4
17.5°	341.6
20°	311.3
22.5°	279.6
25°	253.0
27.5°	226.9
30°	196.1
32.5°	159.9
35°	120.8
37.5°	82.5
40°	51.9
42.5°	31.1
45°	18.4
47.5°	10.6
50°	5.6
52.5°	1.9
55°	1.3
57.5°	1.1
60°	1.1
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)