

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259024

Luminaire Tested: P3AS02R609050DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R609050DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 219.0 lumens  
Efficiency: N/A  
Efficacy: 60.8 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259024  
CATALOG NUMBER: P3AS02R609050DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1259024  
 CATALOG NUMBER: P3AS02R609050DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38878
5°	38433
10°	37118
15°	35051
20°	32319
25°	29252
30°	25979
35°	22192
40°	17662
45°	12435
50°	7437
55°	3747
60°	3596
65°	3321
70°	3077
75°	2965
80°	2652
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12435 cd/sqm



TEST NUMBER: P1259024  
 CATALOG NUMBER: P3AS02R609050DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.4	7.5
10°-20°	43.2	19.7
20°-30°	55.4	25.3
30°-40°	51.4	23.5
40°-50°	31.3	14.3
50°-60°	10.4	4.7
60°-70°	6.4	2.9
70°-80°	3.6	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.0	52.5
0°-40°	166.4	76.0
0°-60°	208.0	95.0
0°-90°	219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	219.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	177	
5°	175	16
15°	154	43
25°	121	55
35°	83	51
45°	40	31
55°	10	10
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1259024  
CATALOG NUMBER: P3AS02R609050DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	177.3
2.5°	176.5
5°	174.6
7.5°	171.2
10°	166.7
12.5°	161.1
15°	154.4
17.5°	146.7
20°	138.5
22.5°	129.7
25°	120.9
27.5°	111.9
30°	102.6
32.5°	93.3
35°	82.9
37.5°	72.0
40°	61.7
42.5°	50.8
45°	40.1
47.5°	31.1
50°	21.8
52.5°	13.0
55°	9.8
57.5°	9.0
60°	8.2
62.5°	7.2
65°	6.4
67.5°	5.6
70°	4.8
72.5°	4.0
75°	3.5
77.5°	2.7
80°	2.1
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)