

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258360

Luminaire Tested: P3AS24R159040D010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R159040D010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1640.0 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258360

CATALOG NUMBER: P3AS24R159040D010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1258360

CATALOG NUMBER: P3AS24R159040D010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	413673
5°	402442
10°	367773
15°	322136
20°	276337
25°	230723
30°	184636
35°	138477
40°	100503
45°	65712
50°	41107
55°	27794
60°	24603
65°	22622
70°	21286
75°	19402
80°	18310
85°	15599

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 65712 cd/sqm

TEST NUMBER: P1258360

CATALOG NUMBER: P3AS24R159040D010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.7	10.3
10°-20°	395.4	24.1
20°-30°	435.6	26.6
30°-40°	326.2	19.9
40°-50°	169.1	10.3
50°-60°	70.1	4.3
60°-70°	43.4	2.6
70°-80°	24.4	1.5
80°-90°	7.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	999.7	61.0
0°-40°	1325.9	80.9
0°-60°	1565.1	95.4
0°-90°	1640.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1640.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1886	
5°	1828	169
15°	1419	395
25°	954	436
35°	517	326
45°	212	169
55°	73	70
65°	44	43
75°	23	24
85°	6	7
90°	0	

TEST NUMBER: P1258360

CATALOG NUMBER: P3AS24R159040D010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1886.5
1°	1888.6
2°	1882.3
3°	1869.9
4°	1851.2
5°	1828.3
6°	1799.2
7°	1768.1
8°	1730.7
9°	1691.2
10°	1651.7
12.5°	1537.4
15°	1419.0
17.5°	1300.6
20°	1184.2
22.5°	1065.8
25°	953.6
27.5°	841.4
30°	729.2
32.5°	619.1
35°	517.3
37.5°	430.1
40°	351.1
42.5°	278.4
45°	211.9
47.5°	160.0
50°	120.5
52.5°	89.3
55°	72.7
57.5°	64.4
60°	56.1
62.5°	49.9
65°	43.6
67.5°	37.4
70°	33.2
72.5°	27.0
75°	22.9
77.5°	18.7
80°	14.5
82.5°	10.4
85°	6.2
87.5°	2.1
90°	0.0

(END OF REPORT)