

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259075

Luminaire Tested: P3AS02R709050DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709050DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 268.1 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259075

CATALOG NUMBER: P3AS02R709050DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1259075

CATALOG NUMBER: P3AS02R709050DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51882
5°	51266
10°	49788
15°	47673
20°	44664
25°	40575
30°	35043
35°	27920
40°	20352
45°	13366
50°	6277
55°	1950
60°	1886
65°	1816
70°	1731
75°	1779
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13366 cd/sqm

TEST NUMBER: P1259075

CATALOG NUMBER: P3AS02R709050DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.9	8.2
10°-20°	58.8	21.9
20°-30°	76.4	28.5
30°-40°	64.8	24.2
40°-50°	33.4	12.5
50°-60°	6.5	2.4
60°-70°	3.5	1.3
70°-80°	2.1	0.8
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.1	58.6
0°-40°	221.9	82.8
0°-60°	261.8	97.7
0°-90°	268.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	237	
5°	233	22
15°	210	59
25°	168	76
35°	104	65
45°	43	33
55°	5	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259075

CATALOG NUMBER: P3AS02R709050DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	236.6
2.5°	235.8
5°	232.9
7.5°	228.6
10°	223.6
12.5°	217.2
15°	210.0
17.5°	201.2
20°	191.4
22.5°	180.2
25°	167.7
27.5°	153.6
30°	138.4
32.5°	121.6
35°	104.3
37.5°	87.3
40°	71.1
42.5°	55.9
45°	43.1
47.5°	31.7
50°	18.4
52.5°	8.0
55°	5.1
57.5°	4.8
60°	4.3
62.5°	4.0
65°	3.5
67.5°	3.2
70°	2.7
72.5°	2.4
75°	2.1
77.5°	1.6
80°	1.3
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)