

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259103

Luminaire Tested: P3AS05R129050DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129050DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 538.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259103

CATALOG NUMBER: P3AS05R129050DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1259103

CATALOG NUMBER: P3AS05R129050DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	459590
5°	407967
10°	283317
15°	167538
20°	95418
25°	54560
30°	30182
35°	16088
40°	8902
45°	4807
50°	3002
55°	2370
60°	2061
65°	1868
70°	1667
75°	1779
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4807 cd/sqm

TEST NUMBER: P1259103

CATALOG NUMBER: P3AS05R129050DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	29.3
10°-20°	208.0	38.7
20°-30°	107.1	19.9
30°-40°	40.2	7.5
40°-50°	13.2	2.4
50°-60°	5.7	1.1
60°-70°	3.6	0.7
70°-80°	2.1	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	472.7	87.9
0°-40°	512.9	95.3
0°-60°	531.7	98.8
0°-90°	538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2096	
5°	1853	158
15°	738	208
25°	226	107
35°	60	40
45°	16	13
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259103

CATALOG NUMBER: P3AS05R129050DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2095.9
1°	2091.8
2°	2064.3
3°	2012.0
4°	1943.0
5°	1853.4
6°	1751.8
7°	1640.3
8°	1516.5
9°	1394.2
10°	1272.4
12.5°	979.0
15°	738.0
17.5°	552.5
20°	408.9
22.5°	305.3
25°	225.5
27.5°	164.3
30°	119.2
32.5°	84.5
35°	60.1
37.5°	43.0
40°	31.1
42.5°	22.3
45°	15.5
47.5°	11.4
50°	8.8
52.5°	7.3
55°	6.2
57.5°	5.2
60°	4.7
62.5°	4.1
65°	3.6
67.5°	3.1
70°	2.6
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)