

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259114

Luminaire Tested: P3AS05R129050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 319.0 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259114

CATALOG NUMBER: P3AS05R129050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259114

CATALOG NUMBER: P3AS05R129050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137555
5°	127140
10°	101512
15°	76663
20°	58385
25°	44495
30°	31878
35°	20800
40°	12738
45°	7722
50°	5117
55°	3976
60°	3421
65°	2958
70°	2629
75°	2626
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7722 cd/sqm

TEST NUMBER: P1259114

CATALOG NUMBER: P3AS05R129050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.2	16.0
10°-20°	94.4	29.6
20°-30°	84.1	26.3
30°-40°	49.7	15.6
40°-50°	20.4	6.4
50°-60°	9.6	3.0
60°-70°	5.8	1.8
70°-80°	3.1	1.0
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.6	72.0
0°-40°	279.4	87.6
0°-60°	309.4	97.0
0°-90°	319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	319.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	627	
5°	578	51
15°	338	94
25°	184	84
35°	78	50
45°	25	20
55°	10	10
65°	6	6
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1259114

CATALOG NUMBER: P3AS05R129050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	627.3
1°	625.8
2°	621.1
3°	611.8
4°	596.2
5°	577.6
6°	557.4
7°	533.6
8°	508.7
9°	483.3
10°	455.9
12.5°	393.2
15°	337.7
17.5°	290.1
20°	250.2
22.5°	215.0
25°	183.9
27.5°	153.9
30°	125.9
32.5°	100.5
35°	77.7
37.5°	59.6
40°	44.5
42.5°	33.2
45°	24.9
47.5°	19.2
50°	15.0
52.5°	12.4
55°	10.4
57.5°	8.8
60°	7.8
62.5°	6.7
65°	5.7
67.5°	5.2
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.1
80°	1.6
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)