

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259135

Luminaire Tested: P3AS05R159050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 212.0 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259135

CATALOG NUMBER: P3AS05R159050DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259135

CATALOG NUMBER: P3AS05R159050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53483
5°	52014
10°	47539
15°	41635
20°	35726
25°	29832
30°	23877
35°	17909
40°	12996
45°	8497
50°	5322
55°	3594
60°	3201
65°	2906
70°	2757
75°	2542
80°	2399
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8497 cd/sqm

TEST NUMBER: P1259135

CATALOG NUMBER: P3AS05R159050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.8	10.3
10°-20°	51.1	24.1
20°-30°	56.3	26.6
30°-40°	42.2	19.9
40°-50°	21.9	10.3
50°-60°	9.1	4.3
60°-70°	5.6	2.6
70°-80°	3.2	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	129.2	61.0
0°-40°	171.4	80.9
0°-60°	202.3	95.4
0°-90°	212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	212.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	244	
5°	236	22
15°	183	51
25°	123	56
35°	67	42
45°	27	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1259135

CATALOG NUMBER: P3AS05R159050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	243.9
1°	244.1
2°	243.3
3°	241.7
4°	239.3
5°	236.3
6°	232.6
7°	228.6
8°	223.7
9°	218.6
10°	213.5
12.5°	198.7
15°	183.4
17.5°	168.1
20°	153.1
22.5°	137.8
25°	123.3
27.5°	108.8
30°	94.3
32.5°	80.0
35°	66.9
37.5°	55.6
40°	45.4
42.5°	36.0
45°	27.4
47.5°	20.7
50°	15.6
52.5°	11.5
55°	9.4
57.5°	8.3
60°	7.3
62.5°	6.4
65°	5.6
67.5°	4.8
70°	4.3
72.5°	3.5
75°	3.0
77.5°	2.4
80°	1.9
82.5°	1.3
85°	0.8
87.5°	0.3
90°	0.0

(END OF REPORT)