

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259192

Luminaire Tested: P3AS05R259050DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259050DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 573.0 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259192

CATALOG NUMBER: P3AS05R259050DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259192

CATALOG NUMBER: P3AS05R259050DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367558
5°	342922
10°	274700
15°	186471
20°	112826
25°	65980
30°	37575
35°	20666
40°	10963
45°	5768
50°	3377
55°	2523
60°	2149
65°	2283
70°	2116
75°	1864
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5768 cd/sqm

TEST NUMBER: P1259192

CATALOG NUMBER: P3AS05R259050DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	24.1
10°-20°	225.8	39.4
20°-30°	129.0	22.5
30°-40°	50.9	8.9
40°-50°	15.6	2.7
50°-60°	6.2	1.1
60°-70°	4.1	0.7
70°-80°	2.3	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.1	86.1
0°-40°	544.0	95.0
0°-60°	565.8	98.8
0°-90°	573.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	573.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1676	
5°	1558	138
15°	821	226
25°	273	129
35°	77	51
45°	19	16
55°	7	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259192

CATALOG NUMBER: P3AS05R259050DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1676.2
1°	1672.9
2°	1659.2
3°	1635.1
4°	1601.7
5°	1557.9
6°	1506.4
7°	1448.4
8°	1381.0
9°	1312.0
10°	1233.7
11°	1156.5
12°	1071.7
13°	987.9
14°	901.9
15°	821.4
17.5°	636.9
20°	483.5
22.5°	363.1
25°	272.7
27.5°	202.1
30°	148.4
32.5°	107.3
35°	77.2
37.5°	54.8
40°	38.3
42.5°	26.3
45°	18.6
47.5°	13.1
50°	9.9
52.5°	7.7
55°	6.6
57.5°	6.0
60°	4.9
62.5°	4.4
65°	4.4
67.5°	3.8
70°	3.3
72.5°	2.7
75°	2.2
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.5



TEST NUMBER: P1259192
CATALOG NUMBER: P3AS05R259050DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)