

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259195

Luminaire Tested: P3AS05R259050DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259050DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 439.0 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259195

CATALOG NUMBER: P3AS05R259050DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1259195

CATALOG NUMBER: P3AS05R259050DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104334
5°	101849
10°	94365
15°	84064
20°	72223
25°	61407
30°	50539
35°	39378
40°	28339
45°	17986
50°	10644
55°	7302
60°	6710
65°	6226
70°	5642
75°	5083
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17986 cd/sqm

TEST NUMBER: P1259195

CATALOG NUMBER: P3AS05R259050DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	9.8
10°-20°	102.8	23.4
20°-30°	116.1	26.5
30°-40°	91.9	20.9
40°-50°	46.4	10.6
50°-60°	18.6	4.2
60°-70°	11.9	2.7
70°-80°	6.6	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.8	59.6
0°-40°	353.7	80.6
0°-60°	418.7	95.4
0°-90°	439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	439.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	476	
5°	463	43
15°	370	103
25°	254	116
35°	147	92
45°	58	46
55°	19	19
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1259195

CATALOG NUMBER: P3AS05R259050DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	475.8
1°	475.8
2°	474.2
3°	471.4
4°	467.6
5°	462.7
6°	456.7
7°	449.6
8°	441.9
9°	433.1
10°	423.8
11°	413.5
12°	403.6
13°	392.1
14°	381.2
15°	370.3
17.5°	339.6
20°	309.5
22.5°	281.1
25°	253.8
27.5°	227.0
30°	199.6
32.5°	173.9
35°	147.1
37.5°	122.5
40°	99.0
42.5°	77.1
45°	58.0
47.5°	43.2
50°	31.2
52.5°	23.5
55°	19.1
57.5°	17.5
60°	15.3
62.5°	13.7
65°	12.0
67.5°	10.4
70°	8.8
72.5°	7.7
75°	6.0
77.5°	4.9
80°	3.8
82.5°	2.7
85°	1.6
87.5°	0.5



TEST NUMBER: P1259195

CATALOG NUMBER: P3AS05R259050DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)