

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259229

Luminaire Tested: P3AS05R309050DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309050DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 445.9 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259229

CATALOG NUMBER: P3AS05R309050DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259229

CATALOG NUMBER: P3AS05R309050DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105364
5°	102993
10°	95790
15°	85222
20°	73296
25°	62108
30°	51552
35°	40448
40°	28969
45°	19010
50°	10814
55°	7111
60°	6710
65°	6226
70°	5642
75°	5083
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19010 cd/sqm

TEST NUMBER: P1259229

CATALOG NUMBER: P3AS05R309050DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	9.7
10°-20°	104.4	23.4
20°-30°	117.6	26.4
30°-40°	93.9	21.1
40°-50°	48.3	10.8
50°-60°	18.2	4.1
60°-70°	11.9	2.7
70°-80°	6.4	1.4
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.4	59.5
0°-40°	359.4	80.6
0°-60°	425.8	95.5
0°-90°	445.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	480	
5°	468	43
15°	375	104
25°	257	118
35°	151	94
45°	61	48
55°	19	18
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1259229

CATALOG NUMBER: P3AS05R309050DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	480.5
1°	480.5
2°	478.9
3°	476.1
4°	472.3
5°	467.9
6°	462.5
7°	455.3
8°	447.7
9°	438.9
10°	430.2
11°	420.3
12°	409.9
13°	399.0
14°	387.5
15°	375.4
17.5°	344.8
20°	314.1
22.5°	284.6
25°	256.7
27.5°	229.3
30°	203.6
32.5°	177.3
35°	151.1
37.5°	125.3
40°	101.2
42.5°	79.9
45°	61.3
47.5°	45.4
50°	31.7
52.5°	22.4
55°	18.6
57.5°	17.0
60°	15.3
62.5°	13.7
65°	12.0
67.5°	10.4
70°	8.8
72.5°	7.1
75°	6.0
77.5°	4.9
80°	3.8
82.5°	2.7
85°	1.6
87.5°	0.5



TEST NUMBER: P1259229

CATALOG NUMBER: P3AS05R309050DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)