

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259257

Luminaire Tested: P3AS05R359050DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259257  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R359050DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 442.0 lumens  
Efficiency: N/A  
Efficacy: 61.4 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259257  
CATALOG NUMBER: P3AS05R359050DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1259257  
 CATALOG NUMBER: P3AS05R359050DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100957
5°	98833
10°	92561
15°	83088
20°	72270
25°	61576
30°	51578
35°	41091
40°	29713
45°	18793
50°	10234
55°	7111
60°	6710
65°	6226
70°	5963
75°	5083
80°	4799
85°	4026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18793 cd/sqm



TEST NUMBER: P1259257  
 CATALOG NUMBER: P3AS05R359050DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.8	9.5
10°-20°	101.8	23.0
20°-30°	116.7	26.4
30°-40°	95.2	21.6
40°-50°	48.0	10.9
50°-60°	17.8	4.0
60°-70°	12.0	2.7
70°-80°	6.6	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.3	58.9
0°-40°	355.6	80.5
0°-60°	421.4	95.3
0°-90°	442.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	442.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	460	
5°	449	42
15°	366	102
25°	254	117
35°	154	95
45°	61	48
55°	19	18
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1259257  
CATALOG NUMBER: P3AS05R359050DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	460.4
1°	459.9
2°	458.8
3°	456.6
4°	453.3
5°	449.0
6°	443.5
7°	438.0
8°	430.9
9°	423.8
10°	415.7
11°	406.9
12°	397.6
13°	387.3
14°	376.3
15°	366.0
17.5°	338.1
20°	309.7
22.5°	280.7
25°	254.5
27.5°	228.9
30°	203.7
32.5°	178.6
35°	153.5
37.5°	128.4
40°	103.8
42.5°	80.8
45°	60.6
47.5°	43.7
50°	30.0
52.5°	21.8
55°	18.6
57.5°	16.9
60°	15.3
62.5°	13.7
65°	12.0
67.5°	10.4
70°	9.3
72.5°	7.6
75°	6.0
77.5°	4.9
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1



TEST NUMBER: P1259257  
CATALOG NUMBER: P3AS05R359050DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)