

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259291

Luminaire Tested: P3AS05R409050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 197.0 lumens
Efficiency: N/A
Efficacy: 27.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259291

CATALOG NUMBER: P3AS05R409050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259291

CATALOG NUMBER: P3AS05R409050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61333
5°	60092
10°	55955
15°	48763
20°	39297
25°	29469
30°	20712
35°	13572
40°	8215
45°	4900
50°	2934
55°	2370
60°	2105
65°	1816
70°	1731
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4900 cd/sqm

TEST NUMBER: P1259291

CATALOG NUMBER: P3AS05R409050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.4	12.9
10°-20°	59.2	30.0
20°-30°	55.8	28.3
30°-40°	32.3	16.4
40°-50°	12.8	6.5
50°-60°	5.7	2.9
60°-70°	3.5	1.8
70°-80°	1.8	0.9
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	140.3	71.2
0°-40°	172.5	87.6
0°-60°	191.1	97.0
0°-90°	197.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	197.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	273	25
15°	215	59
25°	122	56
35°	51	32
45°	16	13
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259291

CATALOG NUMBER: P3AS05R409050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	279.7
2.5°	278.1
5°	273.0
7.5°	263.6
10°	251.3
12.5°	234.7
15°	214.8
17.5°	192.6
20°	168.4
22.5°	144.3
25°	121.8
27.5°	100.8
30°	81.8
32.5°	65.2
35°	50.7
37.5°	38.4
40°	28.7
42.5°	21.5
45°	15.8
47.5°	11.5
50°	8.6
52.5°	7.0
55°	6.2
57.5°	5.6
60°	4.8
62.5°	4.0
65°	3.5
67.5°	3.0
70°	2.7
72.5°	2.1
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)