

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259320

Luminaire Tested: P3AS05R459050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 611.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259320
CATALOG NUMBER: P3AS05R459050DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1259320
 CATALOG NUMBER: P3AS05R459050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229455
5°	224080
10°	205986
15°	174530
20°	135415
25°	94651
30°	59629
35°	35094
40°	19866
45°	9644
50°	3343
55°	2714
60°	2631
65°	2542
70°	2436
75°	2288
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9644 cd/sqm



TEST NUMBER: P1259320
 CATALOG NUMBER: P3AS05R459050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	15.4
10°-20°	211.1	34.6
20°-30°	179.3	29.3
30°-40°	85.5	14.0
40°-50°	25.8	4.2
50°-60°	6.5	1.1
60°-70°	4.9	0.8
70°-80°	2.9	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.6	79.3
0°-40°	570.1	93.3
0°-60°	602.4	98.6
0°-90°	611.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	611.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1046	
5°	1018	94
15°	769	211
25°	391	179
35°	131	86
45°	31	26
55°	7	7
65°	5	5
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1259320
CATALOG NUMBER: P3AS05R459050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1046.4
2.5°	1039.8
5°	1018.0
7.5°	980.3
10°	925.1
12.5°	851.9
15°	768.8
17.5°	676.5
20°	580.3
22.5°	482.5
25°	391.2
27.5°	308.2
30°	235.5
32.5°	177.0
35°	131.1
37.5°	96.7
40°	69.4
42.5°	48.1
45°	31.1
47.5°	17.5
50°	9.8
52.5°	7.6
55°	7.1
57.5°	6.6
60°	6.0
62.5°	5.5
65°	4.9
67.5°	4.4
70°	3.8
72.5°	3.3
75°	2.7
77.5°	2.2
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)