

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258731

Luminaire Tested: P3AS02R129050DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129050DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 203.0 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258731
CATALOG NUMBER: P3AS02R129050DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1258731
 CATALOG NUMBER: P3AS02R129050DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51202
5°	49813
10°	45512
15°	39864
20°	34210
25°	28550
30°	22864
35°	17132
40°	12452
45°	8125
50°	5083
55°	3441
60°	3026
65°	2802
70°	2629
75°	2372
80°	2273
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8125 cd/sqm



TEST NUMBER: P1258731
 CATALOG NUMBER: P3AS02R129050DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.9	10.3
10°-20°	48.9	24.1
20°-30°	53.9	26.6
30°-40°	40.4	19.9
40°-50°	20.9	10.3
50°-60°	8.7	4.3
60°-70°	5.4	2.6
70°-80°	3.0	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	123.7	61.0
0°-40°	164.1	80.8
0°-60°	193.7	95.4
0°-90°	203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	203.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	234	
5°	226	21
15°	176	49
25°	118	54
35°	64	40
45°	26	21
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1258731
CATALOG NUMBER: P3AS02R129050DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	233.5
1°	233.8
2°	233.0
3°	231.5
4°	229.1
5°	226.3
6°	222.7
7°	218.9
8°	214.2
9°	209.3
10°	204.4
12.5°	190.3
15°	175.6
17.5°	161.0
20°	146.6
22.5°	131.9
25°	118.0
27.5°	104.2
30°	90.3
32.5°	76.6
35°	64.0
37.5°	53.2
40°	43.5
42.5°	34.5
45°	26.2
47.5°	19.8
50°	14.9
52.5°	11.1
55°	9.0
57.5°	8.0
60°	6.9
62.5°	6.2
65°	5.4
67.5°	4.6
70°	4.1
72.5°	3.3
75°	2.8
77.5°	2.3
80°	1.8
82.5°	1.3
85°	0.8
87.5°	0.3
90°	0.0

(END OF REPORT)