

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258738

Luminaire Tested: P3AS02R129050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 159.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258738

CATALOG NUMBER: P3AS02R129050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1258738

CATALOG NUMBER: P3AS02R129050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68569
5°	63372
10°	50589
15°	38207
20°	29099
25°	22187
30°	15876
35°	10360
40°	6355
45°	3845
50°	2559
55°	1988
60°	1710
65°	1453
70°	1346
75°	1271
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3845 cd/sqm

TEST NUMBER: P1258738

CATALOG NUMBER: P3AS02R129050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.5	16.0
10°-20°	47.1	29.6
20°-30°	41.9	26.3
30°-40°	24.8	15.6
40°-50°	10.2	6.4
50°-60°	4.8	3.0
60°-70°	2.9	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.5	72.0
0°-40°	139.2	87.5
0°-60°	154.2	97.0
0°-90°	159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	313	
5°	288	26
15°	168	47
25°	92	42
35°	39	25
45°	12	10
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1258738

CATALOG NUMBER: P3AS02R129050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	312.7
1°	311.9
2°	309.6
3°	304.9
4°	297.2
5°	287.9
6°	277.8
7°	265.9
8°	253.6
9°	240.9
10°	227.2
12.5°	196.0
15°	168.3
17.5°	144.6
20°	124.7
22.5°	107.2
25°	91.7
27.5°	76.7
30°	62.7
32.5°	50.1
35°	38.7
37.5°	29.7
40°	22.2
42.5°	16.5
45°	12.4
47.5°	9.6
50°	7.5
52.5°	6.2
55°	5.2
57.5°	4.4
60°	3.9
62.5°	3.4
65°	2.8
67.5°	2.6
70°	2.1
72.5°	1.8
75°	1.5
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)