

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259431

Luminaire Tested: P3AS05R659050DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659050DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 431.0 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259431
CATALOG NUMBER: P3AS05R659050DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1259431
 CATALOG NUMBER: P3AS05R659050DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76704
5°	75677
10°	73123
15°	68967
20°	63612
25°	57753
30°	51147
35°	43527
40°	34636
45°	24437
50°	14191
55°	7761
60°	7192
65°	6538
70°	5963
75°	5592
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24437 cd/sqm



TEST NUMBER: P1259431

CATALOG NUMBER: P3AS05R659050DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.3	7.5
10°-20°	85.0	19.7
20°-30°	109.2	25.3
30°-40°	101.1	23.4
40°-50°	61.0	14.2
50°-60°	20.8	4.8
60°-70°	12.5	2.9
70°-80°	7.1	1.6
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.6	52.6
0°-40°	327.6	76.0
0°-60°	409.4	95.0
0°-90°	431.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	431.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	350	
5°	344	32
15°	304	85
25°	239	109
35°	163	101
45°	79	61
55°	20	21
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1259431
CATALOG NUMBER: P3AS05R659050DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	349.8
2.5°	348.1
5°	343.8
7.5°	337.2
10°	328.4
12.5°	317.5
15°	303.8
17.5°	289.0
20°	272.6
22.5°	255.6
25°	238.7
27.5°	220.6
30°	202.0
32.5°	183.4
35°	162.6
37.5°	142.3
40°	121.0
42.5°	99.6
45°	78.8
47.5°	59.7
50°	41.6
52.5°	26.3
55°	20.3
57.5°	18.1
60°	16.4
62.5°	14.2
65°	12.6
67.5°	10.9
70°	9.3
72.5°	8.2
75°	6.6
77.5°	5.5
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)