

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259432

Luminaire Tested: P3AS05R659050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259432

CATALOG NUMBER: P3AS05R659050DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1259432

CATALOG NUMBER: P3AS05R659050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47277
5°	46093
10°	42930
15°	38479
20°	33230
25°	27631
30°	21801
35°	16142
40°	11135
45°	6915
50°	3753
55°	2370
60°	2017
65°	1816
70°	1539
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6915 cd/sqm

TEST NUMBER: P1259432

CATALOG NUMBER: P3AS05R659050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.5	10.5
10°-20°	47.1	25.3
20°-30°	52.1	28.0
30°-40°	37.8	20.3
40°-50°	17.7	9.5
50°-60°	6.0	3.2
60°-70°	3.4	1.8
70°-80°	1.8	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	118.6	63.8
0°-40°	156.5	84.1
0°-60°	180.2	96.9
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	209	19
15°	170	47
25°	114	52
35°	60	38
45°	22	18
55°	6	6
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259432

CATALOG NUMBER: P3AS05R659050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	215.6
2.5°	214.3
5°	209.4
7.5°	202.2
10°	192.8
12.5°	181.8
15°	169.5
17.5°	156.1
20°	142.4
22.5°	128.2
25°	114.2
27.5°	100.0
30°	86.1
32.5°	72.7
35°	60.3
37.5°	49.1
40°	38.9
42.5°	29.8
45°	22.3
47.5°	16.1
50°	11.0
52.5°	7.5
55°	6.2
57.5°	5.4
60°	4.6
62.5°	4.0
65°	3.5
67.5°	2.9
70°	2.4
72.5°	2.1
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)