

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258785

Luminaire Tested: P3AS02R209050DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258785  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R209050DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 135.0 lumens  
Efficiency: N/A  
Efficacy: 37.5 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258785  
CATALOG NUMBER: P3AS02R209050DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1258785

CATALOG NUMBER: P3AS02R209050DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103873
5°	94409
10°	69783
15°	43156
20°	24642
25°	14081
30°	7900
35°	4283
40°	2347
45°	1302
50°	751
55°	535
60°	526
65°	467
70°	449
75°	424
80°	379
85°	252

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1302 cd/sqm



TEST NUMBER: P1258785

CATALOG NUMBER: P3AS02R209050DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.1	27.5
10°-20°	53.0	39.3
20°-30°	27.7	20.5
30°-40°	10.7	7.9
40°-50°	3.5	2.6
50°-60°	1.4	1.0
60°-70°	0.9	0.7
70°-80°	0.6	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	117.8	87.3
0°-40°	128.5	95.2
0°-60°	133.4	98.8
0°-90°	135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	135.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	474	
5°	429	37
15°	190	53
25°	58	28
35°	16	11
45°	4	3
55°	1	1
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1258785  
CATALOG NUMBER: P3AS02R209050DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	473.7
1°	472.8
2°	467.2
3°	458.5
4°	445.2
5°	428.9
6°	409.6
7°	388.2
8°	363.5
9°	339.3
10°	313.4
12.5°	249.1
15°	190.1
17.5°	142.3
20°	105.6
22.5°	78.2
25°	58.2
27.5°	42.9
30°	31.2
32.5°	22.6
35°	16.0
37.5°	11.6
40°	8.2
42.5°	5.9
45°	4.2
47.5°	3.0
50°	2.2
52.5°	1.7
55°	1.4
57.5°	1.3
60°	1.2
62.5°	1.0
65°	0.9
67.5°	0.8
70°	0.7
72.5°	0.7
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.3
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)