

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259469

Luminaire Tested: P3AS09R159050DE010 E3D1B

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259469  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R159050DE010 E3D1B  
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3D1B TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1033.0 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259469  
CATALOG NUMBER: P3AS09R159050DE010 E3D1B

### Luminous Intensity Polar Plot





TEST NUMBER: P1259469  
 CATALOG NUMBER: P3AS09R159050DE010 E3D1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99  | 99  | 98  | 98  | 98  |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99  | 99  | 98  | 97  | 99  | 98  | 97  | 96  |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  | 100 | 98  | 96  | 98  | 96  | 95  | 98  | 96  | 95  | 94  |
| 4   | 107 | 102 | 99  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 94  | 96  | 94  | 93  | 96  | 94  | 93  | 92  |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  | 96  | 93  | 92  | 94  | 93  | 91  | 94  | 93  | 91  | 90  |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  | 94  | 92  | 90  | 93  | 91  | 89  | 93  | 91  | 89  | 88  |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 90  | 88  | 91  | 89  | 88  | 91  | 89  | 88  | 87  |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  | 91  | 88  | 86  | 90  | 88  | 86  | 90  | 88  | 86  | 85  |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  | 89  | 87  | 85  | 89  | 86  | 85  | 89  | 86  | 85  | 84  |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 87  | 85  | 83  | 82  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1967101 |
| 5°  | 1604046 |
| 10° | 785557  |
| 15° | 240455  |
| 20° | 101836  |
| 25° | 46067   |
| 30° | 17952   |
| 35° | 8272    |
| 40° | 2576    |
| 45° | 961     |
| 50° | 409     |
| 55° | 153     |
| 60° | 175     |
| 65° | 208     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 961 cd/sqm



TEST NUMBER: P1259469  
 CATALOG NUMBER: P3AS09R159050DE010 E3D1B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 567.2  | 54.9      |
| 10°-20°   | 348.1  | 33.7      |
| 20°-30°   | 93.5   | 9.1       |
| 30°-40°   | 20.6   | 2.0       |
| 40°-50°   | 2.9    | 0.3       |
| 50°-60°   | 0.5    | 0.1       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1008.8 | 97.7      |
| 0°-40°    | 1029.4 | 99.6      |
| 0°-60°    | 1032.8 | 100.0     |
| 0°-90°    | 1033.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1033.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8971 |      |
| 5°  | 7287 | 567  |
| 15° | 1059 | 348  |
| 25° | 190  | 93   |
| 35° | 31   | 21   |
| 45° | 3    | 3    |
| 55° | 0    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1259469  
CATALOG NUMBER: P3AS09R159050DE010 E3D1B

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 8970.7 |
| 1°    | 8914.7 |
| 2°    | 8734.9 |
| 3°    | 8411.0 |
| 4°    | 7923.3 |
| 5°    | 7287.2 |
| 6°    | 6567.6 |
| 7°    | 5766.2 |
| 8°    | 5029.8 |
| 9°    | 4249.1 |
| 10°   | 3528.0 |
| 11°   | 2814.4 |
| 12°   | 2165.3 |
| 13°   | 1665.5 |
| 14°   | 1318.5 |
| 15°   | 1059.2 |
| 17.5° | 656.5  |
| 20°   | 436.4  |
| 22.5° | 293.8  |
| 25°   | 190.4  |
| 27.5° | 112.8  |
| 30°   | 70.9   |
| 32.5° | 47.8   |
| 35°   | 30.9   |
| 37.5° | 17.2   |
| 40°   | 9.0    |
| 42.5° | 5.1    |
| 45°   | 3.1    |
| 47.5° | 2.0    |
| 50°   | 1.2    |
| 52.5° | 0.8    |
| 55°   | 0.4    |
| 57.5° | 0.4    |
| 60°   | 0.4    |
| 62.5° | 0.4    |
| 65°   | 0.4    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1259469  
CATALOG NUMBER: P3AS09R159050DE010 E3D1B

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)