

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258810

Luminaire Tested: P3AS02R259050DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259050DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 360.0 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258810

CATALOG NUMBER: P3AS02R259050DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1258810

CATALOG NUMBER: P3AS02R259050DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		97
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		94
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		92
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		89
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		87
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		85
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		83
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		81
9	93	87	83	81	92	87	83	80	86	83	80		85	82	80		79
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	394267
5°	365242
10°	282582
15°	134961
20°	44501
25°	18751
30°	7267
35°	3132
40°	1059
45°	496
50°	171
55°	115
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 496 cd/sqm

TEST NUMBER: P1258810

CATALOG NUMBER: P3AS02R259050DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.8	40.5
10°-20°	165.9	46.1
20°-30°	38.5	10.7
30°-40°	8.1	2.2
40°-50°	1.3	0.4
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	350.3	97.3
0°-40°	358.3	99.6
0°-60°	359.9	100.0
0°-90°	360.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	360.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1798	
5°	1659	146
15°	594	166
25°	78	39
35°	12	8
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258810

CATALOG NUMBER: P3AS02R259050DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1798.0
1°	1794.3
2°	1775.7
3°	1749.4
4°	1709.4
5°	1659.3
6°	1594.9
7°	1527.6
8°	1452.0
9°	1366.7
10°	1269.1
11°	1155.9
12°	1026.1
13°	883.8
14°	735.0
15°	594.5
16°	470.3
17°	366.4
18°	288.2
19°	230.5
20°	190.7
21°	159.4
22°	133.8
23°	111.7
24°	93.5
25°	77.5
27.5°	45.9
30°	28.7
32.5°	18.4
35°	11.7
37.5°	7.0
40°	3.7
42.5°	2.3
45°	1.6
47.5°	0.9
50°	0.5
52.5°	0.3
55°	0.3
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0



TEST NUMBER: P1258810

CATALOG NUMBER: P3AS02R259050DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)