

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259496

Luminaire Tested: P3AS09R209050DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209050DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1009.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259496

CATALOG NUMBER: P3AS09R209050DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1259496

CATALOG NUMBER: P3AS09R209050DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	110		113	112	110	109		108	106	105		104	103	102		101	100	99
2	112	109	107	104		110	108	105	103		104	103	101		102	100	99		99	98	97
3	109	105	102	100		108	104	101	99		102	99	97		99	98	96		97	96	95
4	107	102	99	96		105	101	98	96		99	97	95		97	95	93		96	94	92
5	104	99	96	93		103	98	95	93		97	94	92		95	93	91		94	92	91
6	102	97	93	91		101	96	93	90		95	92	90		94	91	89		93	90	89
7	100	94	91	88		99	94	91	88		93	90	88		92	89	87		91	89	87
8	98	92	89	86		97	92	89	86		91	88	86		90	88	86		89	87	85
9	96	90	87	85		95	90	87	85		89	86	84		89	86	84		88	86	84
10	94	89	85	83		93	88	85	83		88	85	83		87	84	83		86	84	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1567089
5°	1360177
10°	840443
15°	291920
20°	89654
25°	31695
30°	11723
35°	4711
40°	2519
45°	992
50°	546
55°	612
60°	702
65°	415
70°	513
75°	678
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 992 cd/sqm

TEST NUMBER: P1259496

CATALOG NUMBER: P3AS09R209050DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.8	50.8
10°-20°	406.9	40.3
20°-30°	70.5	7.0
30°-40°	12.8	1.3
40°-50°	2.9	0.3
50°-60°	1.4	0.1
60°-70°	0.9	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	990.2	98.1
0°-40°	1003.0	99.4
0°-60°	1007.4	99.8
0°-90°	1009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7146	
5°	6179	513
15°	1286	407
25°	131	70
35°	18	13
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1259496

CATALOG NUMBER: P3AS09R209050DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7146.5
1°	7112.2
2°	6976.4
3°	6758.4
4°	6502.8
5°	6179.3
6°	5808.7
7°	5377.5
8°	4886.3
9°	4334.4
10°	3774.5
12.5°	2380.8
15°	1285.9
17.5°	686.9
20°	384.2
22.5°	219.6
25°	131.0
27.5°	79.9
30°	46.3
32.5°	27.2
35°	17.6
37.5°	12.0
40°	8.8
42.5°	5.6
45°	3.2
47.5°	1.6
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)