

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258831

Luminaire Tested: P3AS02R259050DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259050DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 153.0 lumens
Efficiency: N/A
Efficacy: 42.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258831
CATALOG NUMBER: P3AS02R259050DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1258831

CATALOG NUMBER: P3AS02R259050DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51399
5°	48558
10°	41282
15°	32690
20°	24852
25°	18533
30°	13470
35°	9530
40°	6469
45°	4528
50°	3787
55°	3670
60°	3859
65°	3995
70°	3911
75°	4236
80°	4799
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 5208 cd/sqm



TEST NUMBER: P1258831

CATALOG NUMBER: P3AS02R259050DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	13.0
10°-20°	39.9	26.1
20°-30°	35.3	23.1
30°-40°	22.5	14.7
40°-50°	11.9	7.8
50°-60°	8.7	5.7
60°-70°	7.4	4.9
70°-80°	5.2	3.4
80°-90°	2.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.1	62.2
0°-40°	117.6	76.9
0°-60°	138.2	90.3
0°-90°	153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	234	
5°	221	20
15°	144	40
25°	77	35
35°	36	22
45°	15	12
55°	10	9
65°	8	7
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1258831

CATALOG NUMBER: P3AS02R259050DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	234.4
2.5°	231.0
5°	220.6
7.5°	204.6
10°	185.4
12.5°	164.7
15°	144.0
17.5°	124.1
20°	106.5
22.5°	90.4
25°	76.6
27.5°	64.4
30°	53.2
32.5°	43.7
35°	35.6
37.5°	28.3
40°	22.6
42.5°	18.0
45°	14.6
47.5°	12.6
50°	11.1
52.5°	10.3
55°	9.6
57.5°	9.2
60°	8.8
62.5°	8.0
65°	7.7
67.5°	6.9
70°	6.1
72.5°	5.7
75°	5.0
77.5°	4.2
80°	3.8
82.5°	3.1
85°	1.9
87.5°	0.8
90°	0.0

(END OF REPORT)