

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258866

Luminaire Tested: P3AS02R359050DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258866  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359050DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 338.0 lumens  
Efficiency: N/A  
Efficacy: 93.9 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258866  
CATALOG NUMBER: P3AS02R359050DE010 E3CB1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1258866

CATALOG NUMBER: P3AS02R359050DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	220399
5°	215914
10°	200865
15°	147265
20°	75397
25°	27171
30°	10584
35°	3694
40°	1517
45°	403
50°	375
55°	421
60°	351
65°	259
70°	321
75°	424
80°	379
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 504 cd/sqm



TEST NUMBER: P1258866  
 CATALOG NUMBER: P3AS02R359050DE010 E3CB1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.4	27.1
10°-20°	171.6	50.8
20°-30°	60.7	18.0
30°-40°	10.6	3.1
40°-50°	1.6	0.5
50°-60°	0.9	0.3
60°-70°	0.6	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.7	95.8
0°-40°	334.4	98.9
0°-60°	336.8	99.7
0°-90°	338.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	338.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1005	
5°	981	91
15°	649	172
25°	112	61
35°	14	11
45°	1	2
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1258866  
CATALOG NUMBER: P3AS02R359050DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1005.1
1°	1004.8
2°	1001.6
3°	995.5
4°	989.9
5°	980.9
6°	971.6
7°	961.2
8°	948.4
9°	928.4
10°	902.1
11°	865.6
12°	821.7
13°	769.5
14°	712.0
15°	648.7
17.5°	483.1
20°	323.1
22.5°	194.8
25°	112.3
27.5°	67.1
30°	41.8
32.5°	24.2
35°	13.8
37.5°	8.8
40°	5.3
42.5°	2.7
45°	1.3
47.5°	1.1
50°	1.1
52.5°	1.1
55°	1.1
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0



TEST NUMBER: P1258866  
CATALOG NUMBER: P3AS02R359050DE010 E3CB1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)