

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259549

Luminaire Tested: P3AS09R259050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 46.2 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259549

CATALOG NUMBER: P3AS09R259050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259549

CATALOG NUMBER: P3AS09R259050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186257
5°	178692
10°	156532
15°	125812
20°	96678
25°	73141
30°	52844
35°	35121
40°	21297
45°	12404
50°	7914
55°	6423
60°	5614
65°	4981
70°	4103
75°	4067
80°	3031
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12404 cd/sqm

TEST NUMBER: P1259549

CATALOG NUMBER: P3AS09R259050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	14.4
10°-20°	153.3	29.9
20°-30°	138.6	27.0
30°-40°	83.3	16.2
40°-50°	33.1	6.4
50°-60°	15.3	3.0
60°-70°	9.3	1.8
70°-80°	5.0	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	365.8	71.3
0°-40°	449.0	87.5
0°-60°	497.4	96.9
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	849	
5°	812	74
15°	554	153
25°	302	139
35°	131	83
45°	40	33
55°	17	15
65°	10	9
75°	5	5
85°	2	1
90°	0	

TEST NUMBER: P1259549

CATALOG NUMBER: P3AS09R259050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	849.4
1°	849.4
2°	845.4
3°	836.6
4°	825.4
5°	811.8
6°	794.2
7°	774.2
8°	751.0
9°	727.8
10°	703.0
11°	674.2
12°	644.6
13°	615.0
14°	585.4
15°	554.2
17.5°	480.7
20°	414.3
22.5°	354.3
25°	302.3
27.5°	253.5
30°	208.7
32.5°	168.0
35°	131.2
37.5°	100.0
40°	74.4
42.5°	54.4
45°	40.0
47.5°	30.4
50°	23.2
52.5°	19.2
55°	16.8
57.5°	14.4
60°	12.8
62.5°	10.4
65°	9.6
67.5°	8.0
70°	6.4
72.5°	5.6
75°	4.8
77.5°	4.0
80°	2.4
82.5°	1.6
85°	1.6
87.5°	0.8



TEST NUMBER: P1259549

CATALOG NUMBER: P3AS09R259050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)