

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258898

Luminaire Tested: P3AS02R409050DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409050DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 373.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258898

CATALOG NUMBER: P3AS02R409050DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1258898

CATALOG NUMBER: P3AS02R409050DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	190116
5°	188751
10°	183809
15°	164201
20°	108883
25°	40793
30°	10913
35°	4256
40°	1546
45°	744
50°	239
55°	115
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 744 cd/sqm

TEST NUMBER: P1258898

CATALOG NUMBER: P3AS02R409050DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	21.7
10°-20°	191.7	51.4
20°-30°	86.9	23.3
30°-40°	11.3	3.0
40°-50°	2.0	0.5
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.5	96.4
0°-40°	370.7	99.4
0°-60°	372.9	100.0
0°-90°	373.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	373.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	867	
5°	858	81
15°	723	192
25°	169	87
35°	16	11
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1258898

CATALOG NUMBER: P3AS02R409050DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	867.0
1°	866.5
2°	865.2
3°	863.3
4°	860.8
5°	857.5
6°	853.7
7°	849.0
8°	843.3
9°	835.4
10°	825.5
11°	813.9
12°	798.4
13°	779.2
14°	754.1
15°	723.3
16°	684.0
17°	639.2
18°	585.4
19°	528.6
20°	466.6
21°	404.5
22°	343.4
23°	282.6
24°	222.8
25°	168.6
26°	124.8
27°	91.4
28°	68.7
29°	53.4
30°	43.1
31°	35.6
32°	29.8
32.5°	27.2
33°	24.5
34°	20.0
35°	15.9
36°	12.5
37°	9.9
37.5°	8.9
38°	7.8
39°	6.5
40°	5.4
42.5°	3.5
45°	2.4



TEST NUMBER: P1258898

CATALOG NUMBER: P3AS02R409050DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.4
50°	0.7
52.5°	0.3
55°	0.3
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)