

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259574

Luminaire Tested: P3AS09R309050DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309050DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 651.1 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259574

CATALOG NUMBER: P3AS09R309050DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259574

CATALOG NUMBER: P3AS09R309050DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153803
5°	150341
10°	139810
15°	124405
20°	106993
25°	90658
30°	75252
35°	59026
40°	42308
45°	27755
50°	15795
55°	10399
60°	9824
65°	9132
70°	8207
75°	7456
80°	7072
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27755 cd/sqm

TEST NUMBER: P1259574

CATALOG NUMBER: P3AS09R309050DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.4	9.7
10°-20°	152.3	23.4
20°-30°	171.7	26.4
30°-40°	137.1	21.1
40°-50°	70.5	10.8
50°-60°	26.5	4.1
60°-70°	17.4	2.7
70°-80°	9.4	1.4
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.4	59.5
0°-40°	524.5	80.6
0°-60°	621.6	95.5
0°-90°	651.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	651.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	701	
5°	683	63
15°	548	152
25°	375	172
35°	220	137
45°	90	70
55°	27	27
65°	18	17
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P1259574

CATALOG NUMBER: P3AS09R309050DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	701.4
1°	701.4
2°	699.0
3°	695.0
4°	689.4
5°	683.0
6°	675.0
7°	664.6
8°	653.5
9°	640.7
10°	627.9
11°	613.5
12°	598.3
13°	582.4
14°	565.6
15°	548.0
17.5°	503.3
20°	458.5
22.5°	415.4
25°	374.7
27.5°	334.7
30°	297.2
32.5°	258.8
35°	220.5
37.5°	182.9
40°	147.8
42.5°	116.6
45°	89.5
47.5°	66.3
50°	46.3
52.5°	32.8
55°	27.2
57.5°	24.8
60°	22.4
62.5°	20.0
65°	17.6
67.5°	15.2
70°	12.8
72.5°	10.4
75°	8.8
77.5°	7.2
80°	5.6
82.5°	4.0
85°	2.4
87.5°	0.8



TEST NUMBER: P1259574

CATALOG NUMBER: P3AS09R309050DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)