

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259584

Luminaire Tested: P3AS09R309050DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309050DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 449.0 lumens
Efficiency: N/A
Efficacy: 40.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259584
CATALOG NUMBER: P3AS09R309050DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1259584
 CATALOG NUMBER: P3AS09R309050DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145778
5°	137464
10°	117499
15°	94166
20°	73390
25°	55189
30°	40259
35°	28375
40°	19465
45°	13924
50°	11394
55°	11010
60°	11096
65°	11363
70°	11797
75°	12709
80°	13133
85°	14593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 15456 cd/sqm



TEST NUMBER: P1259584
 CATALOG NUMBER: P3AS09R309050DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.5	12.6
10°-20°	115.3	25.7
20°-30°	105.0	23.4
30°-40°	66.8	14.9
40°-50°	35.8	8.0
50°-60°	26.2	5.8
60°-70°	22.0	4.9
70°-80°	15.4	3.4
80°-90°	6.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.8	61.6
0°-40°	343.6	76.5
0°-60°	405.5	90.3
0°-90°	449.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	449.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	665	
5°	624	57
15°	415	115
25°	228	105
35°	106	67
45°	45	36
55°	29	26
65°	22	22
75°	15	15
85°	6	6
90°	0	



TEST NUMBER: P1259584
CATALOG NUMBER: P3AS09R309050DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	664.8
2.5°	654.4
5°	624.5
7.5°	580.7
10°	527.7
12.5°	471.2
15°	414.8
17.5°	362.9
20°	314.5
22.5°	269.6
25°	228.1
27.5°	191.3
30°	159.0
32.5°	129.0
35°	106.0
37.5°	84.1
40°	68.0
42.5°	54.2
45°	44.9
47.5°	36.9
50°	33.4
52.5°	31.1
55°	28.8
57.5°	27.7
60°	25.3
62.5°	24.2
65°	21.9
67.5°	20.7
70°	18.4
72.5°	16.1
75°	15.0
77.5°	12.7
80°	10.4
82.5°	9.2
85°	5.8
87.5°	2.3
90°	0.0

(END OF REPORT)