

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259639

Luminaire Tested: P3AS09R409050DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409050DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259639

CATALOG NUMBER: P3AS09R409050DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259639

CATALOG NUMBER: P3AS09R409050DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182770
5°	179088
10°	166730
15°	145313
20°	117120
25°	87779
30°	61706
35°	40422
40°	24474
45°	14637
50°	8733
55°	7034
60°	6315
65°	5396
70°	5129
75°	4067
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14637 cd/sqm

TEST NUMBER: P1259639

CATALOG NUMBER: P3AS09R409050DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	12.9
10°-20°	176.3	30.0
20°-30°	166.1	28.3
30°-40°	96.1	16.4
40°-50°	38.3	6.5
50°-60°	17.0	2.9
60°-70°	10.5	1.8
70°-80°	5.5	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.0	71.2
0°-40°	514.1	87.6
0°-60°	569.3	97.0
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	834	
5°	814	76
15°	640	176
25°	363	166
35°	151	96
45°	47	38
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1259639

CATALOG NUMBER: P3AS09R409050DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	833.5
2.5°	828.7
5°	813.6
7.5°	785.6
10°	748.8
12.5°	699.3
15°	640.1
17.5°	573.8
20°	501.9
22.5°	430.0
25°	362.8
27.5°	300.5
30°	243.7
32.5°	194.2
35°	151.0
37.5°	114.3
40°	85.5
42.5°	63.9
45°	47.2
47.5°	34.4
50°	25.6
52.5°	20.8
55°	18.4
57.5°	16.8
60°	14.4
62.5°	12.0
65°	10.4
67.5°	8.8
70°	8.0
72.5°	6.4
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)