

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259651

Luminaire Tested: P3AS09R459050DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459050DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 894.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259651
CATALOG NUMBER: P3AS09R459050DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1259651
 CATALOG NUMBER: P3AS09R459050DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	335719
5°	327866
10°	301397
15°	255370
20°	198141
25°	138492
30°	87254
35°	51370
40°	29054
45°	14141
50°	4912
55°	3976
60°	3859
65°	3736
70°	3590
75°	3389
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14141 cd/sqm



TEST NUMBER: P1259651
 CATALOG NUMBER: P3AS09R459050DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.9	15.4
10°-20°	308.9	34.6
20°-30°	262.3	29.3
30°-40°	125.1	14.0
40°-50°	37.7	4.2
50°-60°	9.6	1.1
60°-70°	7.1	0.8
70°-80°	4.2	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.1	79.3
0°-40°	834.2	93.3
0°-60°	881.5	98.6
0°-90°	894.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	894.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1531	
5°	1490	138
15°	1125	309
25°	572	262
35°	192	125
45°	46	38
55°	10	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1259651
CATALOG NUMBER: P3AS09R459050DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1531.0
2.5°	1521.4
5°	1489.5
7.5°	1434.3
10°	1353.6
12.5°	1246.4
15°	1124.9
17.5°	989.8
20°	849.1
22.5°	706.0
25°	572.4
27.5°	450.9
30°	344.6
32.5°	259.0
35°	191.9
37.5°	141.5
40°	101.5
42.5°	70.4
45°	45.6
47.5°	25.6
50°	14.4
52.5°	11.2
55°	10.4
57.5°	9.6
60°	8.8
62.5°	8.0
65°	7.2
67.5°	6.4
70°	5.6
72.5°	4.8
75°	4.0
77.5°	3.2
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)