

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258932

Luminaire Tested: P3AS02R459050DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1258932  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R459050DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 192.0 lumens  
Efficiency: N/A  
Efficacy: 53.3 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1258932  
CATALOG NUMBER: P3AS02R459050DE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1258932  
 CATALOG NUMBER: P3AS02R459050DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	94	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	86	83	81	79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	81	78	75	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	73	69	66	64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	69	65	61	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	65	61	58	56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	57188
5°	55888
10°	51547
15°	44836
20°	36823
25°	28647
30°	21168
35°	14884
40°	9303
45°	5024
50°	2729
55°	2332
60°	2105
65°	1816
70°	1539
75°	1610
80°	1389
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5024 cd/sqm



TEST NUMBER: P1258932  
 CATALOG NUMBER: P3AS02R459050DE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.5	12.2
10°-20°	54.6	28.4
20°-30°	54.2	28.2
30°-40°	34.9	18.2
40°-50°	13.4	7.0
50°-60°	5.5	2.8
60°-70°	3.5	1.8
70°-80°	1.9	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.3	68.9
0°-40°	167.2	87.1
0°-60°	186.1	96.9
0°-90°	192.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	192.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	261	
5°	254	24
15°	198	55
25°	118	54
35°	56	35
45°	16	13
55°	6	5
65°	4	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1258932  
CATALOG NUMBER: P3AS02R459050DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	260.8
2.5°	259.5
5°	253.9
7.5°	244.3
10°	231.5
12.5°	215.6
15°	197.5
17.5°	177.8
20°	157.8
22.5°	137.6
25°	118.4
27.5°	100.3
30°	83.6
32.5°	68.9
35°	55.6
37.5°	43.6
40°	32.5
42.5°	23.4
45°	16.2
47.5°	10.9
50°	8.0
52.5°	6.7
55°	6.1
57.5°	5.3
60°	4.8
62.5°	4.0
65°	3.5
67.5°	2.9
70°	2.4
72.5°	2.1
75°	1.9
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)