

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259660

Luminaire Tested: P3AS09R459050DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459050DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 694.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259660

CATALOG NUMBER: P3AS09R459050DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259660

CATALOG NUMBER: P3AS09R459050DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147137
5°	144530
10°	136760
15°	124745
20°	110306
25°	95788
30°	82215
35°	68502
40°	51067
45°	31259
50°	14464
55°	11316
60°	10876
65°	9962
70°	9232
75°	8811
80°	8082
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31259 cd/sqm

TEST NUMBER: P1259660

CATALOG NUMBER: P3AS09R459050DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	8.8
10°-20°	153.0	22.0
20°-30°	181.8	26.2
30°-40°	157.9	22.8
40°-50°	79.2	11.4
50°-60°	27.5	4.0
60°-70°	19.3	2.8
70°-80°	10.8	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	396.1	57.1
0°-40°	554.0	79.8
0°-60°	660.7	95.2
0°-90°	694.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	694.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	671	
5°	657	61
15°	550	153
25°	396	182
35°	256	158
45°	101	79
55°	30	28
65°	19	19
75°	10	11
85°	2	3
90°	0	

TEST NUMBER: P1259660

CATALOG NUMBER: P3AS09R459050DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	671.0
2.5°	667.8
5°	656.6
7.5°	639.0
10°	614.2
12.5°	583.9
15°	549.5
17.5°	511.1
20°	472.7
22.5°	433.5
25°	395.9
27.5°	359.9
30°	324.7
32.5°	291.1
35°	255.9
37.5°	218.3
40°	178.4
42.5°	139.2
45°	100.8
47.5°	66.4
50°	42.4
52.5°	32.8
55°	29.6
57.5°	27.2
60°	24.8
62.5°	22.4
65°	19.2
67.5°	16.8
70°	14.4
72.5°	12.0
75°	10.4
77.5°	8.0
80°	6.4
82.5°	4.8
85°	2.4
87.5°	1.6
90°	0.0

(END OF REPORT)