

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259663

Luminaire Tested: P3AS09R459050DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459050DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 577.0 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259663
CATALOG NUMBER: P3AS09R459050DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1259663
 CATALOG NUMBER: P3AS09R459050DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	171872
5°	167950
10°	154929
15°	134711
20°	110680
25°	86110
30°	63579
35°	44758
40°	27938
45°	15133
50°	8187
55°	7034
60°	6315
65°	5396
70°	4616
75°	4745
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15133 cd/sqm



TEST NUMBER: P1259663
 CATALOG NUMBER: P3AS09R459050DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	12.2
10°-20°	164.0	28.4
20°-30°	162.9	28.2
30°-40°	104.9	18.2
40°-50°	40.4	7.0
50°-60°	16.4	2.8
60°-70°	10.4	1.8
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.6	68.9
0°-40°	502.5	87.1
0°-60°	559.3	96.9
0°-90°	577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	577.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	784	
5°	763	71
15°	593	164
25°	356	163
35°	167	105
45°	49	40
55°	18	16
65°	10	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1259663
CATALOG NUMBER: P3AS09R459050DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	783.8
2.5°	779.8
5°	763.0
7.5°	734.2
10°	695.8
12.5°	647.8
15°	593.4
17.5°	534.2
20°	474.3
22.5°	413.5
25°	355.9
27.5°	301.5
30°	251.1
32.5°	207.1
35°	167.2
37.5°	131.2
40°	97.6
42.5°	70.4
45°	48.8
47.5°	32.8
50°	24.0
52.5°	20.0
55°	18.4
57.5°	16.0
60°	14.4
62.5°	12.0
65°	10.4
67.5°	8.8
70°	7.2
72.5°	6.4
75°	5.6
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)