

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258940

Luminaire Tested: P3AS02R459050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 94.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258940

CATALOG NUMBER: P3AS02R459050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1258940

CATALOG NUMBER: P3AS02R459050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28002
5°	27361
10°	25250
15°	21952
20°	18038
25°	14033
30°	10356
35°	7281
40°	4551
45°	2450
50°	1330
55°	1147
60°	1009
65°	882
70°	769
75°	763
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2450 cd/sqm

TEST NUMBER: P1258940

CATALOG NUMBER: P3AS02R459050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.5	12.2
10°-20°	26.7	28.4
20°-30°	26.5	28.2
30°-40°	17.1	18.2
40°-50°	6.6	7.0
50°-60°	2.7	2.8
60°-70°	1.7	1.8
70°-80°	0.9	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	64.8	68.9
0°-40°	81.9	87.1
0°-60°	91.1	96.9
0°-90°	94.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	94.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	128	
5°	124	12
15°	97	27
25°	58	27
35°	27	17
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1258940

CATALOG NUMBER: P3AS02R459050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	127.7
2.5°	127.0
5°	124.3
7.5°	119.6
10°	113.4
12.5°	105.5
15°	96.7
17.5°	87.0
20°	77.3
22.5°	67.4
25°	58.0
27.5°	49.1
30°	40.9
32.5°	33.7
35°	27.2
37.5°	21.4
40°	15.9
42.5°	11.5
45°	7.9
47.5°	5.3
50°	3.9
52.5°	3.3
55°	3.0
57.5°	2.6
60°	2.3
62.5°	2.0
65°	1.7
67.5°	1.4
70°	1.2
72.5°	1.0
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)