

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259680

Luminaire Tested: P3AS09R509050DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509050DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 899.1 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259680
CATALOG NUMBER: P3AS09R509050DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1259680
 CATALOG NUMBER: P3AS09R509050DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.5	13.2
10°-20°	286.5	31.9
20°-30°	281.1	31.3
30°-40°	141.6	15.8
40°-50°	44.7	5.0
50°-60°	11.6	1.3
60°-70°	8.2	0.9
70°-80°	5.1	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.1	76.3
0°-40°	827.7	92.1
0°-60°	884.0	98.3
0°-90°	899.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	899.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1305	
5°	1274	119
15°	1036	286
25°	624	281
35°	217	142
45°	54	45
55°	13	12
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1259680
CATALOG NUMBER: P3AS09R509050DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1305.3
2.5°	1297.3
5°	1274.1
7.5°	1232.6
10°	1179.8
12.5°	1111.9
15°	1035.9
17.5°	948.0
20°	848.1
22.5°	740.2
25°	624.3
27.5°	501.2
30°	387.7
32.5°	291.8
35°	217.4
37.5°	160.7
40°	117.5
42.5°	83.1
45°	54.4
47.5°	31.2
50°	18.4
52.5°	13.6
55°	12.8
57.5°	11.2
60°	10.4
62.5°	9.6
65°	8.0
67.5°	7.2
70°	6.4
72.5°	5.6
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)