

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259688

Luminaire Tested: P3AS09R509050DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509050DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.1 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259688

CATALOG NUMBER: P3AS09R509050DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259688

CATALOG NUMBER: P3AS09R509050DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142247
5°	140149
10°	133954
15°	124064
20°	111496
25°	98014
30°	83355
35°	67592
40°	50781
45°	32717
50°	15522
55°	12234
60°	11578
65°	10792
70°	9745
75°	8811
80°	8082
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32717 cd/sqm

TEST NUMBER: P1259688

CATALOG NUMBER: P3AS09R509050DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	8.5
10°-20°	152.4	21.8
20°-30°	185.1	26.4
30°-40°	157.0	22.4
40°-50°	81.6	11.6
50°-60°	29.5	4.2
60°-70°	20.4	2.9
70°-80°	11.1	1.6
80°-90°	3.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.2	56.7
0°-40°	554.2	79.2
0°-60°	665.2	95.0
0°-90°	700.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	649	
5°	637	60
15°	546	152
25°	405	185
35°	252	157
45°	106	82
55°	32	29
65°	21	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1259688

CATALOG NUMBER: P3AS09R509050DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	648.7
2.5°	646.3
5°	636.7
7.5°	622.4
10°	601.6
12.5°	575.2
15°	546.5
17.5°	513.7
20°	477.8
22.5°	441.0
25°	405.1
27.5°	367.5
30°	329.2
32.5°	290.8
35°	252.5
37.5°	214.9
40°	177.4
42.5°	141.4
45°	105.5
47.5°	70.3
50°	45.5
52.5°	35.2
55°	32.0
57.5°	28.8
60°	26.4
62.5°	23.2
65°	20.8
67.5°	17.6
70°	15.2
72.5°	12.8
75°	10.4
77.5°	8.0
80°	6.4
82.5°	4.8
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)