

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259702

Luminaire Tested: P3AS09R559050DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559050DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1032.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259702
CATALOG NUMBER: P3AS09R559050DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1259702
 CATALOG NUMBER: P3AS09R559050DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299274
5°	288685
10°	298992
15°	294780
20°	272814
25°	220634
30°	132223
35°	44812
40°	12337
45°	5458
50°	1603
55°	306
60°	175
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5458 cd/sqm



TEST NUMBER: P1259702

CATALOG NUMBER: P3AS09R559050DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.9	12.3
10°-20°	361.5	35.0
20°-30°	401.9	38.9
30°-40°	125.1	12.1
40°-50°	15.0	1.5
50°-60°	1.2	0.1
60°-70°	0.4	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.3	86.3
0°-40°	1015.4	98.4
0°-60°	1031.5	100.0
0°-90°	1032.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1032.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1365	
5°	1312	127
15°	1298	362
25°	912	402
35°	167	125
45°	18	15
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1259702
CATALOG NUMBER: P3AS09R559050DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1364.8
1°	1359.7
2°	1346.3
3°	1329.9
4°	1315.0
5°	1311.5
6°	1315.4
7°	1323.6
8°	1333.0
9°	1340.5
10°	1342.8
11°	1341.2
12°	1335.0
13°	1325.2
14°	1313.8
15°	1298.5
16°	1280.9
17°	1258.5
18°	1233.4
19°	1203.2
20°	1169.1
21°	1130.3
22°	1084.4
23°	1033.9
24°	975.8
25°	911.9
26°	841.8
27°	767.3
28°	687.7
29°	605.7
30°	522.2
31°	438.3
32°	356.4
32.5°	319.9
33°	282.3
34°	218.4
35°	167.4
36°	127.4
37°	94.5
37.5°	80.8
38°	70.2
39°	53.3
40°	43.1
42.5°	27.4
45°	17.6



TEST NUMBER: P1259702
CATALOG NUMBER: P3AS09R559050DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	10.6
50°	4.7
52.5°	1.6
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)