

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1258998

Luminaire Tested: P3AS02R559050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1258998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 95.0 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1258998
CATALOG NUMBER: P3AS02R559050DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1258998
 CATALOG NUMBER: P3AS02R559050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	54	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25853
5°	25204
10°	23424
15°	20863
20°	17735
25°	14299
30°	10913
35°	7763
40°	5124
45°	3039
50°	1774
55°	1109
60°	965
65°	882
70°	769
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3039 cd/sqm



TEST NUMBER: P1258998
 CATALOG NUMBER: P3AS02R559050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.6	11.2
10°-20°	25.5	26.8
20°-30°	27.0	28.4
30°-40°	18.2	19.2
40°-50°	8.0	8.4
50°-60°	2.9	3.0
60°-70°	1.7	1.8
70°-80°	0.9	0.9
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	63.1	66.4
0°-40°	81.3	85.6
0°-60°	92.2	97.0
0°-90°	95.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	95.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	118	
5°	114	11
15°	92	25
25°	59	27
35°	29	18
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1258998
CATALOG NUMBER: P3AS02R559050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	117.9
2.5°	116.9
5°	114.5
7.5°	110.4
10°	105.2
12.5°	98.9
15°	91.9
17.5°	84.1
20°	76.0
22.5°	67.5
25°	59.1
27.5°	50.9
30°	43.1
32.5°	35.6
35°	29.0
37.5°	23.0
40°	17.9
42.5°	13.4
45°	9.8
47.5°	7.2
50°	5.2
52.5°	3.7
55°	2.9
57.5°	2.6
60°	2.2
62.5°	2.0
65°	1.7
67.5°	1.4
70°	1.2
72.5°	1.0
75°	0.8
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)