

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259703

Luminaire Tested: P3AS09R559050DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559050DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1032.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259703
CATALOG NUMBER: P3AS09R559050DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1259703

CATALOG NUMBER: P3AS09R559050DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99 | 98 | 97 | 96 | 95 | 95 | 95 | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 92 | 91 | 89 | 89 | 89 | 89 |
| 3 | 104 | 98 | 94 | 90 | 102 | 97 | 93 | 90 | 95 | 91 | 88 | 92 | 89 | 87 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 4 | 100 | 93 | 88 | 84 | 98 | 92 | 87 | 84 | 90 | 86 | 83 | 88 | 84 | 82 | 86 | 83 | 81 | 79 | 79 | 79 | 79 |
| 5 | 95 | 88 | 82 | 79 | 94 | 87 | 82 | 78 | 85 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | 75 | 75 | 75 |
| 6 | 91 | 83 | 78 | 74 | 90 | 82 | 77 | 74 | 81 | 76 | 73 | 80 | 76 | 73 | 78 | 75 | 72 | 71 | 71 | 71 | 71 |
| 7 | 87 | 79 | 73 | 70 | 86 | 78 | 73 | 69 | 77 | 72 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 67 | 67 | 67 | 67 |
| 8 | 83 | 75 | 69 | 66 | 82 | 74 | 69 | 66 | 73 | 69 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 63 | 63 | 63 | 63 |
| 9 | 80 | 71 | 66 | 62 | 79 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 68 | 64 | 61 | 60 | 60 | 60 | 60 |
| 10 | 77 | 68 | 62 | 59 | 76 | 67 | 62 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 65 | 61 | 58 | 57 | 57 | 57 | 57 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 299274 |
| 5° | 288685 |
| 10° | 298992 |
| 15° | 294780 |
| 20° | 272814 |
| 25° | 220634 |
| 30° | 132223 |
| 35° | 44812 |
| 40° | 12337 |
| 45° | 5458 |
| 50° | 1603 |
| 55° | 306 |
| 60° | 175 |
| 65° | 208 |
| 70° | 256 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5458 cd/sqm



TEST NUMBER: P1259703

CATALOG NUMBER: P3AS09R559050DE010 E3D1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 126.9 | 12.3 |
| 10°-20° | 361.5 | 35.0 |
| 20°-30° | 401.9 | 38.9 |
| 30°-40° | 125.1 | 12.1 |
| 40°-50° | 15.0 | 1.5 |
| 50°-60° | 1.2 | 0.1 |
| 60°-70° | 0.4 | 0.0 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 890.3 | 86.3 |
| 0°-40° | 1015.4 | 98.4 |
| 0°-60° | 1031.5 | 100.0 |
| 0°-90° | 1032.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1032.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1365 | |
| 5° | 1312 | 127 |
| 15° | 1298 | 362 |
| 25° | 912 | 402 |
| 35° | 167 | 125 |
| 45° | 18 | 15 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1259703

CATALOG NUMBER: P3AS09R559050DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1364.8 |
| 1° | 1359.7 |
| 2° | 1346.3 |
| 3° | 1329.9 |
| 4° | 1315.0 |
| 5° | 1311.5 |
| 6° | 1315.4 |
| 7° | 1323.6 |
| 8° | 1333.0 |
| 9° | 1340.5 |
| 10° | 1342.8 |
| 11° | 1341.2 |
| 12° | 1335.0 |
| 13° | 1325.2 |
| 14° | 1313.8 |
| 15° | 1298.5 |
| 16° | 1280.9 |
| 17° | 1258.5 |
| 18° | 1233.4 |
| 19° | 1203.2 |
| 20° | 1169.1 |
| 21° | 1130.3 |
| 22° | 1084.4 |
| 23° | 1033.9 |
| 24° | 975.8 |
| 25° | 911.9 |
| 26° | 841.8 |
| 27° | 767.3 |
| 28° | 687.7 |
| 29° | 605.7 |
| 30° | 522.2 |
| 31° | 438.3 |
| 32° | 356.4 |
| 32.5° | 319.9 |
| 33° | 282.3 |
| 34° | 218.4 |
| 35° | 167.4 |
| 36° | 127.4 |
| 37° | 94.5 |
| 37.5° | 80.8 |
| 38° | 70.2 |
| 39° | 53.3 |
| 40° | 43.1 |
| 42.5° | 27.4 |
| 45° | 17.6 |



TEST NUMBER: P1259703
CATALOG NUMBER: P3AS09R559050DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 47.5° | 10.6 |
| 50° | 4.7 |
| 52.5° | 1.6 |
| 55° | 0.8 |
| 57.5° | 0.4 |
| 60° | 0.4 |
| 62.5° | 0.4 |
| 65° | 0.4 |
| 67.5° | 0.4 |
| 70° | 0.4 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)